





POSITIVE AIRWAY PRESSURE (PAP) SYSTEMS

Company		Breas Medical Inc	React Health	ResMed
PAP			 See our ad on page 39	
		Z2 Auto CPAP	Luna G3 AutoCPAP	AirSense 11
Website		www.breas.us	www.reacthealth.com	www.resmed.com
Warranty (years)		2	2	2
Operating Modes		CPAP, APAP	CPAP, APAP	CPAP, APAP
Dimensions (cm)		16.46 x 8.38 x 5.13	26.5 x 14.5 x 11.4	9.45 x 25.94 x 13.85
Weight (kg)		0.295	1.7	1.13
Noise Level (dBA)		26	<26	27
Pressure Range (cm H ₂ O)		4-20	4-20	4-20
Pressure Adjustment Increment (cm H ₂ O)		0.5	0.5	0.2
Max Ramp Time (min)		45	60	45
Adjustable Ramp Settings		5-45 minutes in 5 minute intervals	ramp time, min pressure	Off, 5-45 min, or auto (begins at sleep onset)
Pressure Relief Range/Settings		Z-Breathe-1, Z-Breathe-2, Z-Breathe-3.	0-3 cm H ₂ O in 1 cm increments.	Four EPR settings: 0-3. At 0, pressure relief is turned off. At 3, air pressure is reduced by 3 cm H ₂ O.
Data Recorded		Usage hours, leak, AH count, AHI (index)	Full reporting data including AHI, central apneas, usage time, leak, pressure, P95	Hours used, mode of therapy, apnea (central, obstructive) and hypopnea (AHI), leak, CSR, RERA, pressure, EPR level
Data Transmission Options		Bluetooth	Cellular, Wifi, QR Code, SD card, React Health Connect	Cellular communication, SD card
Power Options		AC input range: 100-240V, DC	AC power code included	AC input range: 100-240V, 50-60Hz, 2.0A
Available Accessories		travel bag	travel case, integrated heated tubing	travel bag, heated and non-heated tubing, SD card, standard and cleanable tub, standard and hypoallergenic filters, end cap
Features	Auto Start/Stop	Yes	Yes	Yes
	Leak Compensation	Yes	Yes	Yes
	Mask On/Off Alert	No	Yes	No
	Altitude Compensation	Yes	Yes	Yes
	Heated Humidification and/or Heat Moisture Exchanger	Yes	Yes	Yes
	Remote Programming	No	Yes	Yes
	Adjustable APAP Algorithm	No	Yes	No
Patient Data Access		Nitelog app	Luna3B QR app	On device; myAir app
Additional Features		Optional PowerShell (integrated overnight battery).	On screen accessory reminder, standby screen saver, Smart A, B, C.	New for Air11: Personal Therapy Assist, Care Check-In (support features designed for support patients starting/staying on treatment), individually toggleable SmartStart & SmartStop. Plus integrated humidifier, advanced event detection, AutoSet response, auto and manual climate control, Remote Assist, AirView, myAir. Algorithms include CPAP, Elite, AutoSet, AutoSet for Her.

Visit www.sleepreviewmag.com/tag/comparison-guides to download this guide as a PDF.

Transcend	
	
Transcend Micro Auto CPAP	
www.mytranscend.com	
2	
CPAP, APAP	
9.1 x 9.1 x 6.1	
0.22	
27	
4-20	
0.1	
45	
0-45 minutes in 5 minute intervals	
Four AirRelief Settings: 0-3 with 3 providing the most relief.	
Therapy hours, apnea/hypopneas, mask leak, pressure, AirRelief	
Bluetooth, USB cable	
AC Power, PowerAway battery, international adapters	
travel bag, PowerAway battery, heat moisture exchanger, WhisperSoft muffler	
Yes	
Yes	
Yes	
Yes	
Yes	
No	
No	
MySleepDash app	
<p>Newly updated MySleepDash, drying mode, micro muffler system for quiet operation. ●</p>	